

Hunter Penrose Supplies Ltd
32 Southwark St, London, SE1 1TU
tel: +44207 407 5051
fax: +44 207 378 1800
carolmatthews@hunterpenrose.co.uk

HUNTER PENROSE

printing materials & equipment

website:
www.hunterpenrose.co.uk

PRODUCT INFORMATION

Product name	Hunterpress FS WEB
Description	Web offset fountain solution
Applications	Coldset web offset printing. (Can also be used for heatset with addition of 8-10% isopropyl alcohol).
Directions for use	For best results empty and thoroughly clean the system. Check and calibrate the metering device. Set the fount dosage at 1.5% for water hardness 4-9dH, 2% for 10-18dH and 3% for 19-24dh. Do not exceed 3%. Reduce water and fount to lowest possible clean printing levels.
Sizes available	25 litres, 200 litres
Tariff code	
Other information	Technical advice and support for individual presses available
P.I. REF	Hunterpress FS Web 0308